

Rittal – The System.

Faster – better – everywhere.



RX 9360.512

RiLineX CB device adapter

State: 5/27/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.512 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. Thanks to the Easy-Fix concept, adapter and switch installation can be carried out independently of each other. This concept is available for all popular manufacturers. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Features

Model No.	RX 9360.512
Version	Easy Fix
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Quick and easy pre-assembly of standard switch types outside the control cabinet
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	Incl. 3 connection compartment covers
Protection category IP to IEC 60529	IP 2XB
Rated impulse withstand voltage U _{Imp}	8 kV

Features

Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage Ui	1,000 V
Contamination level	3
Clamping area for laminated copper bars (W x H)	15 x 6 mm 0.59 x 0.24 "
Number of poles	3-pole
Cable outlet	Bottom
Type of connection (electrical)	Screw M8
To fit manufacturer (model)	ABB (S3 150, S3 225, S3, T3, T4, XT3, XT4, FE160, FE250) Chint (NM8N-250, NM1-250H, NXM-250S, NXMS-250) Eaton (LZMB2-A160, LZMB2-A250) Fuji Electric (BW160_-3P, BW250_-3) Hager (P250) Himel (HDM3-160, HDM3-250, HDM3L-160, HDM3L-250) Hyundai Electric (160, 250AF) Legrand (DPX250, DPX ³ 250) LS Electric (250AF, TS250) Mitsubishi (NF125-SGV, NF160-SGV, NF250-SV) OEZ (BD250) Rockwell (140G-J0F3-D25) Sassin (3SM8N-225, 3SM8L-225) Schneider (EZC250H, NS100, NS160, NS250, NSX100, NSX160, NSX250, GV5) Schrack (MC2) Siemens (3VA20, 3VA21, 3VA22, 3VT2, 3RV1063, 3RV1363, 3RV1364, VL160/3VL2) Terasaki (S160, S250, H250)
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %

Features

Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C -13 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Dimensions	Width: 105 mm Height: 252 mm Depth: 63 mm Width: 4.13 " Height: 9.92 " Depth: 2.48 "
Packaging unit	1 pc(s).
Net weight	1.7 kg
Gross weight	1.792 kg
Copper weight (kg per piece)	0.608
PCF/VE (cradle-to-gate)	10.84
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RX CB device adapter 250 A, 3-pole, version: Easy Fix, cable outlet at bottom, W: 105 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration
