

# Rittal – The System.

Faster – better – everywhere.



## PK 9504.000

## PK Polycarbonate Housings

State: 6/14/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9504.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

|                                    |  |
|------------------------------------|--|
| Model No.                          | PK 9504.000  |
| Version                            | PK housing with closed cover   |
| Product description                | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.   |
| Material                           | Housing: Fiber-glass reinforced polycarbonate<br>Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polythene |
| Color                              | RAL 7035   |
| Supply includes                    | Housing with cover<br>Cover screws<br>Insulating bungs for wall mounting screws  |
| Protection category NEMA           | NEMA 4X  |
| Protection category IP to EN 60529 | IP 66  |

# Features

---

|                             |   |
|-----------------------------|---|
| IK code                     | IK08  |
| Dimensions                  | Width: 94 mm<br>Height: 94 mm<br>Depth: 57 mm<br>Width: 3.7 "<br>Height: 3.7 "<br>Depth: 2.24 "                       |
| Operating temperature range | -35 °C...80 °C<br>-31 °F...176 °F   |
| Base material               | Polycarbonate   |
| Packaging unit              | 6 pc(s).  |
| Net weight                  | 1.002 kg  |
| Gross weight                | 1.072 kg  |
| Customs tariff number       | 84879090  |
| ETIM 9                      | EC000261  |
| ECLASS 8.0                  | 27180101  |
| Product description         | PK Polycarbonate enclosure, WHD: 94x94x57 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover |

---

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | C-UL<br>DNV<br>UL<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity               |

---