

Rittal – The System.

Faster – better – everywhere.



PK 9504.000

PK Polycarbonate Housings

State: 8/28/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9504.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

| | |
|------------------------------------|--|
| Model No. | PK 9504.000 |
| Version | PK housing with closed cover |
| Product description | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment. |
| Material | Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene |
| Color | RAL 7035 |
| Supply includes | Housing with cover Cover screws Insulating bungs for wall mounting screws |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60529 | IP 66 |

Features

| | |
|-----------------------------|---|
| IK code | IK08 |
| Dimensions | Width: 94 mm Height: 94 mm Depth: 57 mm Width: 3.7 " Height: 3.7 " Depth: 2.24 " |
| Operating temperature range | -35 °C...80 °C -31 °F...176 °F |
| Base material | Polycarbonate |
| Packaging unit | 6 pc(s). |
| Net weight | 1.002 |
| Gross weight | 1.072 |
| Customs tariff number | 94037000 |
| EAN | 4028177139091 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|--|
| Approvals | C-UL DNV-GL UL UL + C-UL (listed) |
| Explanations | Declaration of conformity |