Rittal – The System.

Faster – better – everywhere.



PK 9506.000

PK Polycarbonate Housings

State: 11/1/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

PK 9506.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.





Features

Model No.	PK 9506.000
Version	PK housing with closed cover
Product description	Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.
Material	Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws

© Rittal 2026

Features

Dimensions	Width: 110 mm Height: 110 mm Depth: 66 mm Width: 4.33 ″ Height: 4.33 ″ Depth: 2.6 ″
Protection category IP to EN 60 529	IP 66
Protection category NEMA	NEMA 4X
IK code	IK08
Operating temperature range	-35 °C...80 °C -31 °F...176 °F
Base material	Polycarbonate
Packaging unit	6 pc(s).
Net weight	1.242 kg
Gross weight	1.458 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	PK Polycarbonate enclosure, WHD: 110x110x66 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover

Approvals

Approvals	DNV UL + C-UL (listed)
Explanations	Declaration of conformity