

# Rittal – The System.

Faster – better – everywhere.



## PK 9511.000

## PK Polycarbonate Housings

State: 5/15/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9511.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

|                                    |                                                                                                                                                                                      |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                          | PK 9511.000                                                                                                                                                                          |
| Version                            | PK housing with closed cover                                                                                                                                                         |
| Product description                | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.                                                               |
| Material                           | Housing: Fiber-glass reinforced polycarbonate<br>Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polythene |
| Color                              | RAL 7035                                                                                                                                                                             |
| Supply includes                    | Housing with cover<br>Cover screws<br>Insulating bungs for wall mounting screws                                                                                                      |
| Protection category NEMA           | NEMA 4X                                                                                                                                                                              |
| Protection category IP to EN 60529 | IP 66                                                                                                                                                                                |

# Features

---

|                             |                                                                                                                         |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------|
| IK code                     | IK08                                                                                                                    |
| Dimensions                  | Width: 130 mm<br>Height: 130 mm<br>Depth: 99 mm<br>Width: 5.12 "<br>Height: 5.12 "<br>Depth: 3.9 "                      |
| Operating temperature range | -35 °C...80 °C<br>-31 °F...176 °F                                                                                       |
| Base material               | Polycarbonate                                                                                                           |
| Packaging unit              | 4 pc(s).                                                                                                                |
| Net weight                  | 1.464 kg                                                                                                                |
| Gross weight                | 1.64 kg                                                                                                                 |
| Customs tariff number       | 84879090                                                                                                                |
| ETIM 9                      | EC000261                                                                                                                |
| ECLASS 8.0                  | 27180101                                                                                                                |
| Product description         | PK Polycarbonate enclosure, WHD: 130x130x99 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover |

---

# Approvals

---

|              |                                         |
|--------------|-----------------------------------------|
| Approvals    | C-UL<br>DNV<br>UL<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity               |

---