Rittal – The System.

Faster – better – everywhere.



# PK 9513.000

# PK Polycarbonate Housings

State: 10/31/2026 (Source: www.rittal.com/us-en)

# PK 9513.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.





## Features

| | |
|---|---|
| Model No. | PK 9513.000 |
| Version | PK housing with closed cover |
| Product description | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment. |
| Material | Housing: Fiber-glass reinforced polycarbonate<br>Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polythene |
| Color | RAL 7035 |
| Supply includes | Housing with cover<br>Cover screws<br>Insulating bungs for wall mounting screws |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Width: 180 mm<br>Height: 94 mm<br>Depth: 81 mm<br>Width: 7.09 ″<br>Height: 3.7 ″<br>Depth: 3.19 ″ |
| Protection category IP to EN 60 529 | IP 66 |
| Protection category NEMA | NEMA 4X |
| IK code | IK08 |
| Operating temperature range | -35 °C...80 °C<br>-31 °F...176 °F |
| Base material | Polycarbonate |
| Packaging unit | 2 pc(s). |
| Net weight | 0.686 kg |
| Gross weight | 0.8 kg |
| Customs tariff number | 84879090 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | PK Polycarbonate enclosure, WHD: 180x94x81 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover |

# Approvals

| | |
|---|---|
| Approvals | DNV<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity |