

# Rittal – The System.

Faster – better – everywhere.



## PK 9514.000

## PK Polycarbonate Housings

State: 5/30/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9514.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

Model No.	PK 9514.000
Version	PK housing with closed cover
Product description	Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.
Material	Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66

# Features

---

IK code	IK08
Dimensions	Width: 180 mm Height: 110 mm Depth: 90 mm Width: 7.09 " Height: 4.33 " Depth: 3.54 "
Operating temperature range	-35 °C...80 °C -31 °F...176 °F
Base material	Polycarbonate
Packaging unit	2 pc(s).
Net weight	0.786 kg
Gross weight	0.86 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	PK Polycarbonate enclosure, WHD: 180x110x90 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover

# Approvals

---

Approvals	C-UL DNV UL
Explanations	Declaration of conformity