

**Rittal – The System.**

Faster – better – everywhere.



**PK 9515.100**

**PK Polycarbonate Housings**

State: 4/29/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9515.100 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

|                                    |  |
|------------------------------------|--|
| Model No.                          | PK 9515.100  |
| Version                            | PK housing with transparent cover  |
| Product description                | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.   |
| Material                           | Housing: Fiber-glass reinforced polycarbonate<br>Cover transparent: Polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polythene |
| Color                              | RAL 7035   |
| Supply includes                    | Housing with cover<br>Cover screws<br>Insulating bungs for wall mounting screws  |
| Protection category NEMA           | NEMA 4X  |
| Protection category IP to EN 60529 | IP 66  |
| IK code                            | IK08   |

# Features

---

|                             |   |
|-----------------------------|---|
| Dimensions                  | Width: 180 mm<br>Height: 110 mm<br>Depth: 111 mm<br>Width: 7.09 "<br>Height: 4.33 "<br>Depth: 4.37 "                            |
| Operating temperature range | -35 °C...80 °C<br>-31 °F...176 °F   |
| Base material               | Polycarbonate   |
| Packaging unit              | 2 pc(s).  |
| Net weight                  | 0.804 kg  |
| Gross weight                | 1.003 kg  |
| Customs tariff number       | 84879090  |
| ETIM 9                      | EC000261  |
| ECLASS 8.0                  | 27180101  |
| Product description         | PK Polycarbonate enclosure, WHD: 180x110x111 mm, fibreglass-reinforced polycarbonate, without knockouts, with transparent cover |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | C-UL<br>DNV-GL<br>UL      |
| Explanations | Declaration of conformity |

---