

Rittal – The System.

Faster – better – everywhere.



PK 9519.100

PK Polycarbonate Housings

State: 2/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9519.100 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Model No.	PK 9519.100
Version	PK housing with transparent cover
Product description	Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.
Material	Housing: Fiber-glass reinforced polycarbonate Cover transparent: Polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08

Features

Dimensions	Width: 182 mm Height: 180 mm Depth: 165 mm Width: 7.17 " Height: 7.09 " Depth: 6.5 "
------------	---

Operating temperature range	-35 °C...80 °C -31 °F...176 °F
-----------------------------	-----------------------------------

Base material	Polycarbonate
---------------	---------------

Packaging unit	1 pc(s).
----------------	----------

Net weight	0.806
------------	-------

Gross weight	0.906
--------------	-------

Customs tariff number	94037000
-----------------------	----------

EAN	4028177139718
-----	---------------

E-Number Sweden	E3404593
-----------------	----------

ETIM 9	EC000261
--------	----------

ECLASS 8.0	27180101
------------	----------

Approvals

Approvals	C-UL DNV-GL UL
-----------	----------------------

Explanations	Declaration of conformity
--------------	---------------------------
