

Rittal – The System.

Faster – better – everywhere.



PK 9522.000

PK Polycarbonate Housings

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9522.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Model No.	PK 9522.000
Version	PK housing with closed cover
Product description	Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.
Material	Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66

Features

IK code	IK08
Dimensions	Width: 254 mm Height: 180 mm Depth: 165 mm Width: 10 " Height: 7.09 " Depth: 6.5 "
Operating temperature range	-35 °C...80 °C -31 °F...176 °F
Base material	Polycarbonate
Packaging unit	1 pc(s).
Net weight	1 kg
Gross weight	1.164 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	PK Polycarbonate enclosure, WHD: 254x180x165 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover

Approvals

Approvals	C-UL DNV UL
Explanations	Declaration of conformity