

**Rittal – The System.**

Faster – better – everywhere.



**PK 9522.000**

**PK Polycarbonate Housings**

State: 5/13/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9522.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.

## Features

Model No.	PK 9522.000
Applications	Ambient temperature range: -35 °C...+80 °C The specified temperatures can be limited by the installed equipment
Material	Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 254 mm Height: 180 mm Depth: 165 mm Width: 10 " Height: 7.09 " Depth: 6.5 "
Type of cover	gray

# Features

Operating temperature range	-35 °C...80 °C -31 °F...176 °F
Base material	Polycarbonate
Packaging unit	1 pc(s).
Weight/packaging unit	1.16 kg 2.6 lb.
Customs tariff number	94037000
EAN	4028177139817
E-Number Sweden	E3404596
ETIM 7.0	EC000261
ECLASS 8.0	27180101

# Approvals

Approvals	C-UL DNV-GL UL
Explanations	Declaration of conformity