

Rittal – The System.

Faster – better – everywhere.



SV 9612.000

Mini-PLS connection adapter

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9612.000 - Mini-PLS connection adapter

Rated current 63 A/250 A, cable outlet top/bottom.

Features

Model No.	SV 9612.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035 Chassis: RAL 9011
Clamping area for laminated copper bars (W x H)	17 x 15 mm 0.67 x 0.59 "
Note	Wire end ferrules should be used with fine stranded wire conductors
Cable outlet	Top/bottom
Rated operating voltage	690 V
Rated current max.	250 A
Dimensions	Width: 115 mm Height: 182 mm Width: 4.53 " Height: 7.17 "
Connection of round conductors	10 - 120 mm ²
Packaging unit	1 pc(s).
Net weight	0.88 kg
Gross weight	1.096 kg
Copper weight (kg per piece)	0.3
Customs tariff number	85369010
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Mini-PLS busbar connection adaptor, 250 A, 690 V, 3-pole, round conductor connection 10-120 mm ² , clamping area WH: 17x15 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK
