

**Rittal – The System.**

Faster – better – everywhere.



**SV 9612.000**

**Mini-PLS connection adapter**

State: 5/5/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9612.000 - Mini-PLS connection adapter

Rated current 63 A/250 A, cable outlet top/bottom.

## Features

|   |   |
|---|---|
| Model No.                                       | SV 9612.000   |
| Material  | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Color   | RAL 7035<br>Chassis: RAL 9011   |
| Clamping area for laminated copper bars (W x H) | 17 x 15 mm<br>0.67 x 0.59 "   |
| Note  | Wire end ferrules should be used with fine stranded wire conductors   |
| Cable outlet                                    | Top/bottom  |
| Rated operating voltage                         | 690 V   |
| Rated current max.                              | 250 A   |
| Dimensions                                      | Width: 115 mm<br>Height: 182 mm<br>Width: 4.53 "<br>Height: 7.17 "  |
| Connection of round conductors                  | 10 - 120 mm <sup>2</sup>  |
| Packaging unit                                  | 1 pc(s).  |
| Net weight                                      | 0.88 kg   |
| Gross weight                                    | 1.096 kg  |
| Copper weight (kg per piece)                    | 0.3   |
| Customs tariff number                           | 85369010  |
| ETIM 9  | EC001531  |
| ECLASS 8.0                                      | 27370304  |
| Product description                             | SV Mini-PLS busbar connection adaptor, 250 A, 690 V, 3-pole, round conductor connection 10-120 mm <sup>2</sup> , clamping area WH: 17x15 mm |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---