

# Rittal – The System.

Faster – better – everywhere.



## SV 9625.000

# Mini-PLS Component Adaptor

State: 4/30/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9625.000 - Mini-PLS Component Adaptor

Maximum rated current from 12 A to 100 A.

## Features

Model No.	SV 9625.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Connection cables (AWG)	AWG 12
Rated operating voltage	690 V, 3~
Rated current max.	25 A
Dimensions	Width: 72 mm Height: 160 mm Width: 2.83 " Height: 6.3 "
Support rails Qty/height	1 / 7.5 mm 0.3 "
Packaging unit	1 pc(s).
Net weight	0.3 kg
Gross weight	0.373 kg
Copper weight (kg per piece)	0.041
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 72x160 mm, support rail H: 7,5 mm

# Approvals

---

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

---