

# Rittal – The System.

Faster – better – everywhere.



## SV 9640.940 Threaded Bolts

State: 4/5/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9640.940 - Threaded Bolts for sliding blocks and sliding nuts

For fastening connection components such as cable lugs.

## Features

Model No.	SV 9640.940
Product description	For individual connection options.
Material	Steel
Supply includes	Assembly components
Suitable for busbars	Maxi-PLS 45 S/45 Maxi-PLS 60
Dimensions	Thread: M8 Thread length: 35 mm Thread: M8 Thread length: 1.38 "
Packaging unit	6 pc(s).
Net weight	0.102 kg
Gross weight	0.109 kg
Customs tariff number	73181535
ETIM 9	EC002349
ECLASS 8.0	23110302
Product description	SV Threaded bolt, M8, L: 35 mm

## Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------