

Rittal – The System.

Faster – better – everywhere.



SV 9666.732

Depth stay

State: 4/29/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.732 - Depth stay For ISV installation kit

For attaching the ISV installation kit in the enclosure.

Features

Model No.	SV 9666.732
Product description	For attaching the installation kit in the enclosure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Suitable for Model No.	9666.902 9666.912 9666.922 9666.932
Suitable for	Enclosure type: VX Depth: = 400 mm = 500 mm = 600 mm Enclosure type: VX Depth: = 15.7 " = 19.7 " = 23.6 "
Packaging unit	2 pc(s).
Net weight	3.04 kg
Gross weight	3.04 kg
PCF/VE (cradle-to-gate)	12.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002270
ECLASS 8.0	27400613

Features

Product description

VX Depth stay (ISV), (depth 400/500/600 mm),