

Rittal – The System.

Faster – better – everywhere.



TS 9672.169 Partial Doors

State: 5/15/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 9672.169 - Partial Doors for TS

Door may be optionally hinged on the right or left.



Features

Model No.	TS 9672.169
Version	with viewing window
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high.
Material	Carbon steel, 2 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Textured paint
Color	RAL 7035

Features

Supply includes	Cross member Hinges Lock components Assembly components
Dimensions	Width: 600 mm Height: 800 mm Width: 23.6 " Height: 31.5 "
Suitable for	Width: = 600 mm Width: = 23.6 "
Protection category IP to IEC 60529	IP 54 for a completed enclosure
Packaging unit	1 pc(s).
Weight/packaging unit	8.3 kg 18.3 lb.
Customs tariff number	94039910
EAN	4028177697898
ETIM 7.0	EC000747
ECLASS 8.0	27182204