

# Rittal – The System.

Faster – better – everywhere.



## TS 9672.181 Partial Doors

State: 5/22/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 9672.181 - Partial Doors for TS

Door may be optionally hinged on the right or left.



## Features

|                     |   |
|---------------------|---|
| Model No.           | TS 9672.181   |
| Product description | Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high. |
| Material            | Carbon steel, 2 mm  |
| Surface finish      | Textured paint  |
| Color               | RAL 7035  |
| Supply includes     | Cross member<br>Hinges<br>Lock components<br>Assembly components  |

# Features

|                                     |  |
|-------------------------------------|--|
| Dimensions                          | Width: 800 mm<br>Height: 150 mm<br>Width: 31.5 “<br>Height: 5.91 “ |
| Suitable for                        | Width: = 800 mm<br>Width: = 31.5 “                                 |
| Protection category IP to IEC 60529 | IP 54 for a completed enclosure                                    |
| Packaging unit                      | 1 pc(s).   |
| Weight/packaging unit               | 3.48 kg<br>7.7 lb.   |
| Customs tariff number               | 94039910   |
| EAN                                 | 4028177697782  |
| ETIM 7.0                            | EC000747   |
| ECLASS 8.0                          | 27182204   |