

Rittal – The System.

Faster – better – everywhere.



TS 9672.181 Partial Doors

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

TS 9672.181 - Partial Doors for TS

Door may be optionally hinged on the right or left.



Features

| | |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | TS 9672.181 |
| Product description | Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high. |
| Material | Carbon steel, 2 mm |
| Surface finish | Textured paint |
| Color | RAL 7035 |
| Supply includes | Cross member Hinges Lock components Assembly components |

Features

| | |
|-------------------------------------|--------------------------------------------------------------------|
| Dimensions | Width: 800 mm Height: 150 mm Width: 31.5 " Height: 5.91 " |
| Suitable for | Width: = 800 mm Width: = 31.5 " |
| Protection category IP to IEC 60529 | IP 54 for a completed enclosure |
| Packaging unit | 1 pc(s). |
| Net weight | 3.378 kg |
| Gross weight | 3.578 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002525 |
| ECLASS 8.0 | 27182204 |
| Product description | SV Partial door, WH: 800x150 mm, for TS |