
Rittal – The System.

Faster – better – everywhere.



SV 9676.971
Threaded Bolts

State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9676.971 - Threaded Bolts for sliding blocks and sliding nuts

For fastening connection components such as cable lugs.

Features

Model No.	SV 9676.971
Product description	For individual connection options.
Material	Steel
Supply includes	Assembly components
Suitable for busbars	Maxi-PLS 45 S/45 Maxi-PLS 60
Dimensions	Thread: M10 Thread length: 35 mm Thread: M10 Thread length: 1.38 ″
Packaging unit	8 pc(s).
Net weight	0.248 kg
Gross weight	0.259 kg
Customs tariff number	73181535
ETIM 9	EC002349
ECLASS 8.0	23110302
Product description	SV Threaded bolt, M10, L: 35 mm

Approvals

Approvals	UL + C-UL (listed)

© Rittal 2026