

Rittal – The System.

Faster – better – everywhere.



SV 9676.981

Threaded Bolts

State: 2/12/2026 (Source: ittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.981 - Threaded Bolts for sliding blocks and sliding nuts

For fastening connection components such as cable lugs.

Features

| | |
|-----------------------|---|
| Model No. | SV 9676.981 |
| Product description | For individual connection options. |
| Material | Steel |
| Supply includes | Assembly components |
| Suitable for busbars | Maxi-PLS 60 |
| Dimensions | Thread: M12 Thread length: 40 mm Thread: M12 Thread length: 1.57 " |
| Packaging unit | 8 pc(s). |
| Net weight | 0.4 |
| Gross weight | 0.409 |
| Customs tariff number | 73181535 |
| EAN | 4028177606913 |
| ETIM 9 | EC002349 |
| ECLASS 8.0 | 23110302 |

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|