

# Rittal – The System.

Faster – better – everywhere.



## SV 9676.987 Threaded Bolts

State: 8/28/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9676.987 - Threaded Bolts for sliding blocks and sliding nuts

For fastening connection components such as cable lugs.

## Features

Model No.	SV 9676.987
Product description	For individual connection options.
Material	Steel
Supply includes	Assembly components
Suitable for busbars	Maxi-PLS 60
Dimensions	Thread: M12 Thread length: 80 mm Thread: M12 Thread length: 3.15 "
Packaging unit	8 pc(s).
Net weight	0.6
Gross weight	0.645
Customs tariff number	73181535
EAN	4028177606951
ETIM 9	EC002349
ECLASS 8.0	23110302

## Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------