

Rittal – The System.

Faster – better – everywhere.



SV 9677.450

Contact terminal

State: 2/12/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.450 - Contact terminal For NH in-line fuse-switch disconnectors/connector adapters

For mounting components on busbar systems with 185 mm center-to-center spacing, no drilling required.

Features

Model No.	SV 9677.450
Product description	For mounting components on busbar systems with 185 mm center-to-center spacing, no drilling required.
Material	Carbon steel, zinc-plated E-Cu, tin-plated
For size	00
Note	Only suitable for use on busbar system with contact hazard protection cover (cover section, slotted)
Packaging unit	3 pc(s).
Net weight	0.225
Gross weight	0.24
Copper weight (kg per piece)	0.038
PCF/VE (cradle-to-gate)	0.8 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73182900
EAN	4028177705197
ETIM 9	EC000001
ECLASS 8.0	27141146