

**Rittal – The System.**

Faster – better – everywhere.



**SV 9681.548**

**Roof plates for cable entry glands**

State: 6/2/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9681.548 - Roof plates for cable entry glands for VX, VX IT

For enclosures without roof plate and to replace the standard roof on other enclosures.

## Features

Model No.	SV 9681.548
Product description	For enclosures without roof plate and to replace the standard roof.
Material	Carbon steel, 1.5 mm
Surface finish	Textured paint
Color	RAL 7035
Supply includes	Assembly components
Number of required cable entry glands	4
Suitable for	Width: = 400 mm Depth: = 800 mm Width: = 15.7 " Depth: = 31.5 "
Packaging unit	1 pc(s).
Net weight	2.62 kg
Gross weight	3.42 kg
PCF/VE (cradle-to-gate)	13 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
ETIM 9	EC000744
ECLASS 8.0	27182405
Product description	VX Roof plate, Wdepth 400x800 mm, for cable entry glands

# Approvals

---

Explanations

Declaration of conformity UK