
Rittal - The System.

Faster – better – everywhere.





SV 9681.566 Roof plates for cable entry glands

State: 11/15/2025 (Source: rittal.com/us-en)



SV 9681.566 - Roof plates for cable entry glands for VX, VX IT

For enclosures without roof plate and to replace the standard roof on other enclosures.

Features

| Model No. | SV 9681.566 |
|---------------------------------------|---|
| Product description | For enclosures without roof plate and to replace the standard roof. |
| Material | Carbon steel, 1.5 mm |
| Surface finish | Textured paint |
| Color | RAL 7035 |
| Supply includes | Assembly components |
| Number of required cable entry glands | 4 |
| Suitable for | Width: = 600 mm Depth: = 600 mm Width: = 23.6 " Depth: = 23.6 " |
| Packaging unit | 1 pc(s). |
| Net weight | 3.5 |
| Gross weight | 4 |
| PCF/VE (cradle-to-gate) | 15.2 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| EAN | 4028177926608 |
| ETIM 9 | EC000744 |
| ECLASS 8.0 | 27182405 |

© Rittal 2025

Approvals

Explanations

Declaration of conformity UK

© Rittal 2025 3