
Rittal – The System.

Faster – better – everywhere.



# SV 9682.188

# Partial door

State: 11/15/2026 (Source: www.rittal.com/us-en)

# SV 9682.188 - Partial door for VX

Door may be optionally hinged on the right or left.

## Features

| | |
|---|---|
| Model No. | SV 9682.188 |
| Product description | Suitable for VX enclosures instead of a door or rear panel. The partial doors can be combined with each other. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. Installation of the SZ 2305.000 monitor frame is possible in doors without a viewing window (height 600–1,000 mm). The standard double-bit lock insert may be exchanged for Type A lock inserts. |
| Material | Carbon steel, 2 mm |
| Surface finish | Textured paint |
| Color | RAL 7035 |
| Supply includes | Partial door<br>Cross member<br>Hinges<br>Lock components<br>Assembly components |
| Note | Swing angle of partial doors max. 130° |
| Lock | No. of locks: 2 |
| Dimensions | Width: 800 mm<br>Height: 800 mm<br>Width: 31.5 ″<br>Height: 31.5 ″ |
| Suitable for | Width: = 800 mm<br>Width: = 31.5 ″ |
| Protection category IP to IEC 60 529 | IP 54 |
| Packaging unit | 1 pc(s). |
| Net weight | 12.86 kg |

© Rittal 2026

# Features

| | |
|---|---|
| Gross weight | 13.16 kg |
| PCF/VE (cradle-to-gate) | 50.1 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |
| Product description | VX Partial door, WH: 800x800 mm sheet steel |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed)<br>UL + C-UL - FTTA |