
Rittal – The System.

Faster – better – everywhere.



SV 9683.564
Partial Mounting Panel

State: 11/5/2026 (Source: www.rittal.com/us-en)

SV 9683.564 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

Features

Model No.	SV 9683.564
Version	with insulating material gland
Product description	For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible.
Material	Carbon steel, 2 mm
Surface finish	Zinc-plated
Supply includes	Angle brackets and assembly components
For compartment height	400 mm 15.7 ″
Dimensions	Width: 502 mm Height: 393 mm Width: 19.8 ″ Height: 15.5 ″
Suitable for	Width: = 600 mm Width: = 23.6 ″
Packaging unit	1 pc(s).
Net weight	4.2 kg
Gross weight	4.7 kg
PCF/VE (cradle-to-gate)	17.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910

© Rittal 2026

Features

ETIM 9	EC000213
ECLASS 8.0	27400613
Product description	SV Partial mounting plate, WH: 502x393 mm, with duct, for VX (W: 600 mm)