Rittal – The System.

Faster – better – everywhere.



# SV 9683.626

# Partial Mounting Panel

State: 11/6/2026 (Source: www.rittal.com/us-en)

# SV 9683.626 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

## Features

| | |
|---|---|
| Model No. | SV 9683.626 |
| Version | Solid |
| Product description | For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible. |
| Material | Carbon steel, 2 mm |
| Surface finish | Zinc-plated |
| Supply includes | Angle brackets and assembly components |
| For compartment height | 600 mm<br>23.6 ″ |
| Dimensions | Width: 1,102 mm<br>Height: 593 mm<br>Width: 43.4 ″<br>Height: 23.3 ″ |
| Suitable for | Width: = 1,200 mm<br>Width: = 47.2 ″ |
| Packaging unit | 1 pc(s). |
| Net weight | 13 kg |
| Gross weight | 13.46 kg |
| PCF/VE (cradle-to-gate) | 51.3 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |

© Rittal 2026

# Features

| | |
|---|---|
| ETIM 9 | EC000213 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Partial mounting plate, WH: 1102x593 mm, solid, for VX (W: 1200 mm) |