

Rittal – The System.

Faster – better – everywhere.



SV 9683.662 Partial Mounting Panel

State: 6/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9683.662 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

Features

| | |
|-------------------------------------|---|
| Model No. | SV 9683.662 |
| Version | Solid |
| Product description | For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible. |
| Material | Carbon steel, 2 mm |
| Surface finish | Zinc-plated |
| Supply includes | Angle brackets and assembly components |
| For compartment height | 200 mm 7.87 " |
| Dimensions | Width: 502 mm Height: 193 mm Width: 19.8 " Height: 7.6 " |
| Suitable for | Width: = 600 mm Width: = 23.6 " |
| Packaging unit | 1 pc(s). |
| Net weight | 2.35 kg |
| Gross weight | 2.7 kg |
| PCF/VE (cradle-to-gate) | 10.3 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |

Features

| | |
|---------------------|--|
| ETIM 9 | EC000213 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Partial mounting plate, WH: 502x193 mm, solid, for VX (W: 600 mm) |
