

Rittal – The System.

Faster – better – everywhere.



SV 9683.681

Partial Mounting Panel

State: 2/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9683.681 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

Features

| | |
|-------------------------------------|---|
| Model No. | SV 9683.681 |
| Version | Solid |
| Product description | For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible. |
| Material | Carbon steel, 2 mm |
| Surface finish | Zinc-plated |
| Supply includes | Angle brackets and assembly components |
| For compartment height | 150 mm 5.91 " |
| Dimensions | Width: 702 mm Height: 143 mm Width: 27.6 " Height: 5.63 " |
| Suitable for | Width: = 800 mm Width: = 31.5 " |
| Packaging unit | 1 pc(s). |
| Net weight | 2.4 |
| Gross weight | 2.76 |
| PCF/VE (cradle-to-gate) | 10.5 kg CO ₂ eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |

Features

EAN 4028177935266

ETIM 9 EC000213

ECLASS 8.0 27400613

Approvals

Explanations Declaration of conformity UK