## Rittal – The System.

Faster – better – everywhere.





# SV 9683.686 Partial Mounting Panel

State: 11/17/2025 (Source: rittal.com/us-en)



# SV 9683.686 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

#### **Features**

Model No.	SV 9683.686
Version	Solid
Product description	For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible.
Material	Carbon steel, 2 mm
Surface finish	Zinc-plated
Supply includes	Angle brackets and assembly components
For compartment height	600 mm 23.6 ″
Dimensions	Width: 702 mm  Height: 593 mm  Width: 27.6 "  Height: 23.3 "
Suitable for	Width: = 800 mm Width: = 31.5 "
Packaging unit	1 pc(s).
Net weight	9.5
Gross weight	10
PCF/VE (cradle-to-gate)	38.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910

© Rittal 2025

### **Features**

EAN	4028177936942
ETIM 9	EC000213
ECLASS 8.0	27400613

# **Approvals**

Explanations Declaration of conformity UK

© Rittal 2025 3