
Rittal – The System.

Faster – better – everywhere.



SV 9684.004




Busbar E-Cu, slotted

State: 11/5/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9684.004 - Busbar E-Cu, slotted

Features

Model No.	SV 9684.004
Product description	Busbars with integrated holes.
Material	E-Cu
Standards	DIN EN 13 601
Cross-section	50 mm x 10 mm 1.97 ″ x 0.39 ″
Hole diameter	11.5 mm
Dimensions	Length: 385 mm Length: 15.2 ″
Packaging unit	1 pc(s).
Net weight	1.68 kg
Gross weight	1.78 kg
Copper weight (kg per piece)	1.68
Customs tariff number	74071000
ETIM 9	EC001522
ECLASS 8.0	27370303
Product description	SV busbars E-Cu with integral punchings, length 385 mm

© Rittal 2026

Approvals

Approvals	DNV Lloyds Register UL + C-UL (listed)