

Rittal – The System.

Faster – better – everywhere.



SV 9686.030 Busbar Supports

State: 6/1/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9686.030 - Busbar Supports for busbar rows (roof section)

For baying busbar systems in the roof section from enclosure to enclosure.

Features

Model No.	SV 9686.030
Product description	For baying 3- or 4-pole flat copper busbar systems from enclosure to enclosure in the roof section.
Material	Duroplastic Fire protection corresponding to UL 94-V0
Color	Similar to RAL 9005
Supply includes	Assembly components
Suitable for busbars	50 x 10
Center-to-center spacing of busbars	80 mm
Mounting tip	A maximum of 4 busbars (strands) may be installed per phase Cage nut (M8) 4165.500 is required to attach the busbar support to the enclosure section.
Packaging unit	2 pc(s).
Net weight	3 kg
Customs tariff number	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV busbar holder (baying), 4-pole, 80 mm, for E-Cu 50 x 10 mm, duroplastic, fire protection in accordance with UL 94-V0

Approvals

Approvals

Approvals

DNV
Lloyds Register

Explanations

Declaration of conformity UK