Rittal – The System.

Faster – better – everywhere.





SV 9686.030 **Busbar Supports**

State: 11/16/2025 (Source: rittal.com/us-en)



SV 9686.030 - Busbar Supports for busbar rows (roof section)

For baying busbar systems in the roof section from enclosure to enclosure.

Features

Model No.	SV 9686.030
Product description	For baying 3- or 4-pole flat copper busbar systems from enclosure to enclosure in the roof section.
Material	Duroplastic Fire protection corresponding to UL 94-V0
Color	Similar to RAL 9005
Supply includes	Assembly components
Suitable for busbars	50 x 10
Center-to-center spacing of busbars	80 mm
Mounting tip	A maximum of 4 busbars (strands) may be installed per phase Cage nut (M8) 4165.500 is required to attach the busbar support to the enclosure section.
Packaging unit	2 pc(s).
Net weight	3
Customs tariff number	85469010
EAN	4028177935655
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

© Rittal 2025

Approvals

Approvals	DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity UK

© Rittal 2025 3