Rittal – The System.

Faster – better – everywhere.



SV 9686.060
Busbar Supports

State: 11/12/2026 (Source: www.rittal.com/us-en)

SV 9686.060 - Busbar Supports for busbar rows (rear section)

For baying busbar systems in the rear section from enclosure to enclosure.

Features

Model No.	SV 9686.060
Product description	For baying 3-pole flat copper busbar systems in the rear section from enclosure to enclosure.
Material	Duroplastic Fire protection corresponding to UL 94-V0
Color	Similar to RAL 9005
Supply includes	Assembly components
Suitable for busbars	50 x 10
Center-to-center spacing of busbars	185 mm
Mounting tip	A maximum of 4 busbars (strands) may be installed per phase Cage nut (M8) 4165.500 is required to attach the busbar support to the enclosure section.
Packaging unit	2 pc(s).
Net weight	2.7 kg
Gross weight	3.04 kg
Customs tariff number	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV busbar holder (baying), 3-pole, 185 mm, for E-Cu 50 x 10 mm, duroplastic, fire protection in accordance with UL 94-V0

© Rittal 2026

Approvals

Approvals	UL + C-UL (listed)