## Rittal – The System.

Faster – better – everywhere.





# CS 9751.918 Multifunction housing

State: 11/19/2025 (Source: rittal.com/us-en)



## CS 9751.918 - Multifunction housing

Double-walled housing for outdoor installation made of aluminum with resistance class RC2.



#### **Features**

Model No.	CS 9751.918
Product description	3-door, double-walled housing for outdoor installation made of aluminum with resistance class RC 2. Includes cable management base/plinth. Prepared to accept 19"/ETSI combination rails and a Direct Air Cooling System (DAC).
Material	Housing, roof, door(s), base plate: Aluminum, AlMg3, 2.0 mm Mounting plate(s): Aluminum, AlMg3, 3.0 mm Support rail: Stainless steel 1.4016 (AISI 430)
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035
Supply includes	Double-walled outdoor housing, fully preconfigured Weather protection roof with ventilation, prepared for the installation of a Direct Air Cooling System (DAC) Door stay using mechanical system (approx. 155°) Swing lever handle and semi-cylinder, lock BJ20027 Cable routing base, planked all around Flange Plates Gland plate Including 4 mounting plates Screwed-in middle bar Welded-in middle bar Center door locked from the inside

© Rittal 2025

### Features

Width: 2,000 mm  Height: 1,050 mm  Depth: 500 mm  Width: 78.7 "  Height: 41.3 "  Depth: 19.7 "
Overall height: 1,600 mm  Rain canopy height: 130 mm  Height of base/plinth: 400 mm  Rain canopy height: 5.12 "  Height of base/plinth: 15.7 "
548 mm x 941 mm 548 mm x 941 mm 375 mm x 941 mm 280 mm x 941 mm 21.6 " x 37" 21.6 " x 37" 14.8 " x 37"
3
Lock version: 3-point locking system with single and double locking cylinder No. of locks: 3 Lock Insert: BJ20027
Size: 2 Qty.: 4
IP 55
NEMA 3R
NEMA 12
NEMA 12  The door opening angle is approx. 155° in the left and right doors, and approx. 110° in the middle door.
The door opening angle is approx. 155° in the left and right doors,
The door opening angle is approx. 155° in the left and right doors, and approx. 110° in the middle door.

© Rittal 2025 3

#### **Features**

Net weight	175
Gross weight	195
EAN	4028177980846
ETIM 9	EC000261

© Rittal 2025