

Rittal – The System.

Faster – better – everywhere.



CS 9781.860

Sidewalls, Screw-Fastened

State: 5/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9781.860 - Sidewalls, Screw-Fastened for CS Toptec, bayable

Double-walled, screwable side panel, including roof side panels.

Features

Model No.	CS 9781.860
Material	Aluminum AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035
Supply includes	Side Panels Roof side parts Incl. grounding and assembly components
Suitable for	Enclosure type: CS Toptec, bayable Height: = 1,800 mm Depth: = 600 mm Enclosure type: CS Toptec, bayable Height: = 70.9 " Depth: = 23.6 "
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 3R NEMA 12
Base material	Aluminum
Packaging unit	2 pc(s).
Net weight	36 kg
Gross weight	48.5 kg
Customs tariff number	94039910
ETIM 9	EC002524
ETIM 8	EC002524

Features

ECLASS 8.0

27182101

Product description

CS Side panel, double-walled, for HD: 1800x600 mm, aluminum
AlMg3