

# Rittal – The System.

Faster – better – everywhere.



## CS 9783.510

## Outdoor Basic enclosure

State: 12/21/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9783.510 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles



## Features

|                     |  |
|---------------------|--|
| Model No.           | CS 9783.510  |
| Product description | Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides.   |
| Material            | Aluminum AlMg3   |
| Surface finish      | Powder-coated<br>UV-resistant pure polyester   |
| Color               | RAL 7035   |
| Supply includes     | Single-walled outdoor enclosure, fully preconfigured<br>Basic enclosure with gland plate, three-part<br>25 mm system punchings in the roof, base, front and in the enclosure depth<br>Front door(s) with door stay, swing lever handle and semi-cylinder, lock BJ20027<br>Transport plinth with screw-fastened trim panels front and rear<br>Rain canopy |

# Features

|                                      |   |
|--------------------------------------|---|
| Dimensions                           | Width: 800 mm<br>Height: 800 mm<br>Depth: 400 mm<br>Width: 31.5 "<br>Height: 31.5 "<br>Depth: 15.7 "  |
| Dimensions                           | Overall height: 955 mm<br>Rain canopy width: 850 mm<br>Rain canopy height: 55 mm<br>Rain canopy depth: 450 mm<br>Clearance width: 712 mm<br>Clearance height: 712 mm<br>Clearance depth: 349 mm<br>Height of base/plinth: 100 mm<br>Rain canopy width: 33.5 "<br>Rain canopy height: 2.17 "<br>Rain canopy depth: 17.7 "<br>Clearance width: 28 "<br>Clearance height: 28 "<br>Clearance depth: 13.7 "<br>Height of base/plinth: 3.94 " |
| Type rating according to UL 50E      | Type 3R   |
| Protection category IP to IEC 60 529 | IP 55   |
| IK code                              | IK10  |
| Base material                        | Aluminum  |
| Packaging unit                       | 1 pc(s).  |
| Net weight                           | 37  |
| Gross weight                         | 38  |
| EAN                                  | 4028177569119   |
| ETIM 9                               | EC000261  |
| ECLASS 8.0                           | 27180101  |