

Rittal – The System.

Faster – better – everywhere.



CS 9783.520

Outdoor Basic enclosure

State: 4/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9783.520 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles



Features

| | |
|---------------------|--|
| Model No. | CS 9783.520 |
| Product description | Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides. |
| Material | Aluminum AlMg3 |
| Surface finish | Powder-coated UV-resistant pure polyester |
| Color | RAL 7035 |
| Supply includes | Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and semi-cylinder, lock BJ20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy |

Features

| | |
|------------|--|
| Dimensions | Width: 800 mm Height: 1,200 mm Depth: 400 mm Width: 31.5 " Height: 47.2 " Depth: 15.7 " |
|------------|--|

| | |
|------------|---|
| Dimensions | Overall height: 1,355 mm Rain canopy width: 850 mm Rain canopy height: 55 mm Rain canopy depth: 450 mm Clearance width: 712 mm Clearance height: 1,112 mm Clearance depth: 349 mm Height of base/plinth: 100 mm Rain canopy width: 33.5 " Rain canopy height: 2.17 " Rain canopy depth: 17.7 " Clearance width: 28 " Clearance height: 43.8 " Clearance depth: 13.7 " Height of base/plinth: 3.94 " |
|------------|---|

| | |
|---------------------------------|---------|
| Type rating according to UL 50E | Type 3R |
|---------------------------------|---------|

| | |
|--------------------------------------|-------|
| Protection category IP to IEC 60 529 | IP 55 |
|--------------------------------------|-------|

| | |
|---------|------|
| IK code | IK10 |
|---------|------|

| | |
|---------------|----------|
| Base material | Aluminum |
|---------------|----------|

| | |
|----------------|----------|
| Packaging unit | 1 pc(s). |
|----------------|----------|

| | |
|------------|-------|
| Net weight | 46 kg |
|------------|-------|

| | |
|--------------|-------|
| Gross weight | 48 kg |
|--------------|-------|

| | |
|-----------------------|----------|
| Customs tariff number | 94032080 |
|-----------------------|----------|

| | |
|--------|----------|
| ETIM 9 | EC000261 |
|--------|----------|

| | |
|------------|----------|
| ECLASS 8.0 | 27180101 |
|------------|----------|
