

Rittal – The System.

Faster – better – everywhere.



CS 9783.540

Outdoor Basic enclosure

State: 3/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9783.540 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles



Features

Model No.	CS 9783.540
Product description	Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides.
Material	Aluminum AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and semi-cylinder, lock BJ20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy

Features

Dimensions	Width: 600 mm Height: 800 mm Depth: 400 mm Width: 23.6 " Height: 31.5 " Depth: 15.7 "
------------	--

Dimensions	Overall height: 955 mm Rain canopy width: 650 mm Rain canopy height: 55 mm Rain canopy depth: 450 mm Clearance width: 512 mm Clearance height: 712 mm Clearance depth: 349 mm Height of base/plinth: 100 mm Rain canopy width: 25.6 " Rain canopy height: 2.17 " Rain canopy depth: 17.7 " Clearance width: 20.2 " Clearance height: 28 " Clearance depth: 13.7 " Height of base/plinth: 3.94 "
------------	---

Type rating according to UL 50E	Type 3R
---------------------------------	---------

Protection category IP to IEC 60 529	IP 55
--------------------------------------	-------

IK code	IK10
---------	------

Base material	Aluminum
---------------	----------

Packaging unit	1 pc(s).
----------------	----------

Net weight	29 kg
------------	-------

Gross weight	34 kg
--------------	-------

Customs tariff number	94032080
-----------------------	----------

ETIM 9	EC000261
--------	----------

ECLASS 8.0	27180101
------------	----------
