Rittal – The System.

Faster – better – everywhere.





CS 9783.610 **Outdoor Basic enclosure**

State: 12/10/2025 (Source: rittal.com/us-en)



CS 9783.610 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles







Features

Model No.	CS 9783.610
Product description	Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides.
Material	Aluminum AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and semi-cylinder, lock BJ20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy

© Rittal 2025

Features

Dimensions	Width: 800 mm
	Height: 1,200 mm
	Depth: 500 mm
	Width: 31.5 "
	Height: 47.2 "
	Depth: 19.7 "
Dimensions	Overall height: 1,355 mm
	Rain canopy width: 850 mm
	Rain canopy height: 55 mm
	Rain canopy depth: 550 mm
	Clearance width: 712 mm
	Clearance height: 1,112 mm
	Clearance depth: 449 mm
	Height of base/plinth: 100 mm
	Rain canopy width: 33.5 "
	Rain canopy height: 2.17 "
	Rain canopy depth: 21.7 "
	Clearance width: 28 "
	Clearance height: 43.8 "
	Clearance depth: 17.7 "
	Height of base/plinth: 3.94 ″
Number of doors	1
Type rating according to UL 50E	Type 3R
Protection category IP to IEC 60	IP 55
529	
IK code	IK10
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	34
Gross weight	36.15
EAN	4028177569171
ETIM 9	EC000261
ECLASS 8.0	27180101

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

© Rittal 2025