

Rittal – The System.

Faster – better – everywhere.



CS 9791.035

Outdoor Wall-mounted enclosure

State: 2/5/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))



FRIEDHELM LOH GROUP

CS 9791.035 - Outdoor Wall-mounted enclosure

Outdoor housings for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation.



Features

Model No.	CS 9791.035
Product description	Outdoor housings for wall or pole mounting. Housing-within-a-housing concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation
Material	Enclosure and mounting plate: Aluminum AlMg3 Door inner casing: Stainless steel 1.4301 (AISI 304)
Surface finish	Housing: powder-coated, UV-resistant pure polyester
Color	RAL 7035
Supply includes	Double-walled outdoor housing, fully preconfigured Inner enclosure with mounting plate, gland plate and security lock Mounting bracket for enclosure internal thermostat or hygrostat Outer housing with designer cover and security lock 3524 E 2 C rails on the rear panel
Dimensions	Width: 530 mm Height: 700 mm Depth: 265 mm Width: 20.9 " Height: 27.6 " Depth: 10.4 "

Features

Clearances	Clearance width: 440 mm Clearance height: 545 mm Clearance depth: 195 mm Clearance width: 17.3 “ Clearance height: 21.5 “ Clearance depth: 7.68 “
Dimensions of mounting plate (W x H)	430 mm x 535 mm 16.9 “ x 21.1 “
Inner housing	Width: 460 mm Height: 565 mm Depth: 220 mm Width: 18.1 “ Height: 22.2 “ Depth: 8.66 “
Lock	Lock version: Cam No. of locks: 2
Protection category IP to IEC 60529	IP 55
Note	Delivery times on request.
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	16.625
Gross weight	17.5
Customs tariff number	94032080
EAN	4028177193710
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK