Rittal – The System.

Faster – better – everywhere.



AX 9792.055

Outdoor enclosure

State: 11/1/2026 (Source: www.rittal.com/us-en)

AX 9792.055 - Outdoor enclosure for AX wallmount enclosure

Housing for AX compact enclosures for outdoor use, consisting of enclosure shell, rear panel, base and plug-in door. For creating an enclosure-within-an-enclosure concept. Cut-out at the bottom and integrated louvres in the side and base for optimum enclosure ventilation.





Features

Model No.	AX 9792.055
Product description	Housing for AX compact enclosures, for use outdoors. For creating an enclosure-within-an-enclosure concept. Cut-out at the bottom and integrated louvres in the side and base for optimum enclosure ventilation.
Benefits	Housing for AX compact enclosures, for use outdoors For creating an enclosure-within-an-enclosure concept Cut-out at the bottom and integrated louvres in the side and base for optimum enclosure ventilation
Material	Aluminum AlMg3
Surface finish	Powder-coated
Supply includes	Support rails for wall mounting Brush strip Stepped collar M25 Cam lock with 3 mm double-bit insert Incl. grounding and assembly components

Features

Note	Depending on the application/environment, a carbon steel or stainless steel enclosure may be built into the housing
Dimensions	Width: 421 mm Height: 550 mm Depth: 308 mm Width: 16.6 ″ Height: 21.7 ″ Depth: 12.1 ″
Suitable for	Enclosure type: AX Width: = 300 mm Height: = 400 mm Depth: = 210 mm Enclosure type: AX Width: = 11.8 ″ Height: = 15.7 ″ Depth: = 8.27 ″
Packaging unit	1 pc(s).
Net weight	10.5 kg
Gross weight	11.1 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	Outdoor encapsulation for AX wall-mounted enclosures, WHD: 300 x 400 x 210 mm

© Rittal 2026