

Rittal – The System.

Faster – better – everywhere.



VX 9840.307

VX Hybrid Double Door, NEMA 4X

State: 5/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9840.307 - VX Hybrid Double Door, NEMA 4X Stainless steel

The VX Hybrid Double Door is a robust yet lightweight enclosure solution, perfect for applications where simple, quick deployment, portability, and safety are critical. The removable mullion allows for a single mounting panel and ample space for installing and removal of the panel. With corrosive resistant NEMA 4X rating, these enclosures have a place in nearly endless applications.



Features

| | |
|----------------|--|
| Model No. | VX 9840.307 |
| Material | Housing: Stainless steel 1.4301 (AISI 304) Enclosure frame: Stainless steel 1.4301 (AISI 304), 1.5 mm Roof: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Door: Stainless steel 1.4301 (AISI 304), 2.0 mm, exterior brushed Side/rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Base plates: Stainless steel 1.4301 (AISI 304), 1.5 mm Mounting panel: Carbon steel, 3.0 mm |
| Surface finish | Enclosure frame: Uncoated Door, roof and rear panel: Exterior brushed, grain size 400 Mounting panel: Zinc-plated |

Features

| | |
|--------------------------------------|--|
| Supply includes | <p>Enclosure frame</p> <p>Doors - center latched, can be hinged left or right</p> <p>Roof plate with overlapping sides. Back and drip shield</p> <p>Base, solid</p> <p>Rear panels</p> <p>Side Panels</p> <p>Center mullion - removable</p> <p>Heavy-duty padlockable handle</p> <p>4 punched rails 18 x 39 mm</p> <p>Mounting panel</p> |
| Dimensions | <p>Width: 1,800 mm</p> <p>Height: 1,800 mm</p> <p>Depth: 600 mm</p> <p>Width: 70.9 "</p> <p>Height: 70.9 "</p> <p>Depth: 23.6 "</p> |
| Dimensions of mounting plate (W x H) | <p>1,702 mm x 1,696 mm</p> <p>67 " x 66.8 "</p> |
| Usable depth | <p>455.5 mm</p> <p>17.9 "</p> |
| Protection category IP to EN 60 529 | IP 66 |
| Protection category NEMA | NEMA 4X |
| Type rating according to UL 50E | Type 1, 3R, 4X, 12 |
| Number of doors | 2 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 643.6 lb |
| Gross weight | 643.6 lb |
| Product description | VX Hybrid Double Door, Nema 4X, internally fastened hardware used for all components (rear panel, side panel, roof, base plate) stainless steel, 71" x 71" x 24" |

Approvals

Approvals

UL + C-UL (listed)