

Rittal – The System.

Faster – better – everywhere.



VX 9840.308

VX Hybrid Double Door

State: 6/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9840.308 - VX Hybrid Double Door Stainless steel

The VX Hybrid Double Door is a robust yet lightweight enclosure solution, perfect for applications where simple, quick deployment, portability, and safety are critical. The removable mullion allows for a single mounting panel and ample space for installing and removal of the panel. With corrosive resistant NEMA 4X rating, these enclosures have a place in nearly endless applications.



Features

Model No.	VX 9840.308
Material	Housing: Stainless steel 1.4301 (AISI 304) Enclosure frame: Stainless steel 1.4301 (AISI 304), 1.5 mm Roof: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Door: Stainless steel 1.4301 (AISI 304), 2.0 mm, exterior brushed Side/rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Base plates: Stainless steel 1.4301 (AISI 304), 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: Uncoated Door, roof and rear panel: Exterior brushed, grain size 400 Mounting panel: Zinc-plated
Supply includes	Enclosure frame Doors - center latched, can be hinged left or right Roof plate with overlapping sides. Back and drip shield Base, solid Rear panels Side Panels Center mullion - removable Heavy-duty padlockable handle 4 punched rails 18 x 39 mm Mounting panel

Features

Dimensions	Width: 1,800 mm Height: 2,000 mm Depth: 600 mm Width: 70.9 " Height: 78.7 " Depth: 23.6 "
Dimensions of mounting plate (W x H)	1,702 mm x 1,896 mm 67 " x 74.6 "
Usable depth	455.5 mm 17.9 "
Protection category IP to EN 60 529	IP 66
Protection category NEMA	NEMA 4X
Type rating according to UL 50E	Type 1, 3R, 4X, 12
Number of doors	2
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	699.2 lb
Gross weight	699.2 lb
Product description	VX Hybrid Double Door, Nema 4X, internally fastened hardware used for all components (rear panel, side panel, roof, base plate) stainless steel, 79" x 71" x 24"

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------