Rittal – The System.

Faster – better – everywhere.



# VX 9840.309

# VX Hybrid Double Door

State: 11/9/2026 (Source: www.rittal.com/us-en)


ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# VX 9840.309 - VX Hybrid Double Door Stainless steel

The VX Hybrid Double Door is a robust yet lightweight enclosure solution, perfect for applications where simple, quick deployment, portability, and safety are critical. The removable mullion allows for a single mounting panel and ample space for installing and removal of the panel. With corrosive resistant NEMA 4X rating, these enclosures have a place in nearly endless applications.







## Features

| | |
|---|---|
| Model No. | VX 9840.309 |
| Material | Housing: Stainless steel 1.4301 (AISI 304)<br>Enclosure frame: Stainless steel 1.4301 (AISI 304), 1.5 mm<br>Roof: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed<br>Door: Stainless steel 1.4301 (AISI 304), 2.0 mm, exterior brushed<br>Side/rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed<br>Base plates: Stainless steel 1.4301 (AISI 304), 1.5 mm<br>Mounting panel: Carbon steel, 3.0 mm |
| Surface finish | Enclosure frame: Uncoated<br>Door, roof and rear panel: Exterior brushed, grain size 400<br>Mounting panel: Zinc-plated |
| Supply includes | Enclosure frame<br>Doors - center latched, can be hinged left or right<br>Roof plate with overlapping sides. Back and drip shield<br>Base, solid<br>Rear panels<br>Side Panels<br>Center mullion - removable<br>Heavy-duty padlockable handle<br>4 punched rails 18 x 39 mm<br>Mounting panel |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Width: 1,800 mm<br>Height: 2,200 mm<br>Depth: 600 mm<br>Width: 70.9 ″<br>Height: 86.6 ″<br>Depth: 23.6 ″ |
| Dimensions of mounting plate (W x H) | 1,702 mm x 2,096 mm<br>67 ″ x 82.5 ″ |
| Usable depth | 455.5 mm<br>17.9 ″ |
| Protection category IP to EN 60 529 | IP 66 |
| Protection category NEMA | NEMA 4X |
| Type rating according to 508A | Type 1, 3R, 4X, 12 |
| Number of doors | 2 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 754.7 lb |
| Gross weight | 754.7 lb |
| Product description | VX Hybrid Double Door, Nema 4X, internally fastened hardware used for all components (rear panel, side panel, roof, base plate) stainless steel, 87" x 71" x 24" |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |