## Rittal – The System.

Faster – better – everywhere.






# WM 9851.538 WM wall-mounted enclosure

State: 12/14/2025 (Source: rittal.com/us-en)



# WM 9851.538 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



#### **Features**

Model No.	WM 9851.538
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
Color	Mounting panel: Zinc-plated  RAL 7035
Supply includes	Housing with door(s)  Door hinged on left  Mounting plate  Rear wall mounting holes
Dimensions	Width: 400 mm Height: 600 mm Depth: 250 mm Width: 15.7 " Height: 23.6 " Depth: 9.84 "
Dimensions of mounting plate (W x H)	354 mm x 570 mm 13.9 " x 22.4 "

© Rittal 2025 2

### Features

Protection category NEMA	NEMA 1
	NEMA 3R
	NEMA 4
	NEMA 12
Packaging unit	1 pc(s).
Net weight	28.999
Gross weight	28.999
Customs tariff number	8538100000
UPC-Code	91194

# **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3