Rittal – The System.

Faster – better – everywhere.



WM 9956.505
Deep Hinged Window Kits

State: 11/13/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

WM 9956.505 - Deep Hinged Window Kits Carbon steel

The Deep-Hinged Window Kit (WKDH) is used as a cover where access to components mounted on the enclosure door is required. It is designed to protect HMI displays and other components from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal’s Nema 3R Vented Outdoor Enclosures. The depth allows for use of extra deep pushbuttons (~2”/50mm). It comes with a full-size drill template for easy mounting.

Features

Model No.	WM 9956.505
Product description	The Deep-Hinged Window Kit (WKDH) is used as a cover where access to components mounted on the enclosure door is required. It is designed to protect HMI displays and other components from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal’s Nema 3R Vented Outdoor Enclosures. The depth allows for use of extra deep pushbuttons (~2”/50mm). It comes with a full-size drill template for easy mounting.
Material	Frame: Carbon steel
Surface finish	Dipcoat-primed and powder-coated, textured paint
Color	RAL 9003
Supply includes	Oil resistant gasket Fasteners
Dimensions	Width: 300 mm Height: 300 mm Depth: 70 mm Width: 11.8 ˝ Height: 11.8 ˝ Depth: 2.76 ˝
Packaging unit	1 pc(s).

Approvals

Approvals

Approvals	UL + C-UL (listed)