

Rittal – The System.

Faster – better – everywhere.



IT 9962.853 TS IT Colo

State: 4/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 9962.853 - TS IT Colo

TS IT Colo is preconfigured for rapid deployment in colocation environments. 482.6 mm (19") interior installation with depth-variable 482.6 mm (19") profile rails for a load capacity of up to 3,300lbs.



Features

Model No.	IT 9962.853
Product description	TS IT Colo, 19" mounting angles, vented, WHD: 600 x 2200 x 1200 mm, 47 U
Material	Carbon steel
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 9005
Color	Enclosure frame and panels: RAL 9005 Interior installation: RAL 9005

Features

Supply includes	<p>Enclosure frame TS 8 with front and rear doors</p> <p>Carbon steel front door, ventilated, 130° hinges</p> <p>Rear door made of carbon steel, divided, vented, 130° hinges</p> <p>Lock front and rear: Comfort handle with 3-digit code and security lock 3524 E</p> <p>Front and rear 482.6 mm (19") Z-rail mounting sections, depth adjustable mounting</p> <p>Connection accessories for potential equalization with earthing point (supplied loose)</p> <p>M6 cage nuts (Package of 50)</p> <p>50 multi-tooth screws, conductive (supplied loose)</p> <p>IPPC pallet</p> <p>Roof plate, multi-piece, removable, with full depth side cable entry</p> <p>Solid partition wall</p> <p>Cable management wall, pre-installed</p> <p>Vertical brush baffles</p> <p>Dual PDU button mount bracket</p> <p>Baying kit</p> <p>Leveling feet (Package of 4 shipped loose)</p>
Dimensions	<p>Width: 600 mm</p> <p>Height: 2,200 mm</p> <p>Depth: 1,200 mm</p> <p>Width: 23.6 "</p> <p>Height: 86.6 "</p> <p>Depth: 47.2 "</p>
Height units	47 U
Distance between levels as delivered	742 mm 29.2 "
Number front doors	1
Number back doors	1
19" attachment	Front and rear 482.6 mm (19") Z-rail mounting sections, depth adjustable mounting
Design of rear door	Perforated Dual Door, Carbon Steel
Design for front door	Perforated Door, Carbon Steel
Load capacity	15,000 N

Features

Note	The door-opening angle may vary depending on site requirements or applications
Packaging unit	1 pc(s).
Net weight	380.071 lb
Gross weight	380.071 lb
Customs tariff number	9403200082
