Rittal – The System.

Faster – better – everywhere.



IT 9962.854

TS IT Colo

State: 11/16/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

IT 9962.854 - TS IT Colo

TS IT Colo is preconfigured for rapid deployment in colocation environments. 482.6 mm (19") interior installation with depth-variable 482.6 mm (19") profile rails for a load capacity of up to 3,300lbs.





Features

Model No.	IT 9962.854
Product description	TS IT Colo, 19" mounting angles, vented, WHD: 800 x 2200 x 1200 mm, 47 U
Material	Carbon steel
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 9005
Color	Enclosure frame and panels: RAL 9005 Interior installation: RAL 9005

© Rittal 2026

Features

Supply includes	Enclosure frame TS 8 with front and rear doors Carbon steel front door, ventilated, 130° hinges Rear door made of carbon steel, divided, vented, 130° hinges Lock front and rear: Comfort handle with 3-digit code and security lock 3524 E Front and rear 482.6 mm (19") Z-rail mounting sections, depth adjustable mounting Connection accessories for potential equalization with earthing point (supplied loose) M6 cage nuts (Package of 50) 50 multi-tooth screws, conductive (supplied loose) IPPC pallet Roof plate, multi-piece, removable, with full depth side cable entry Solid partition wall Cable management wall, pre-installed Vertical brush baffles Dual PDU button mount bracket Baying kit Leveling feet (Package of 4 shipped loose)
Dimensions	Width: 800 mm Height: 2,200 mm Depth: 1,200 mm Width: 31.5 ″ Height: 86.6 ″ Depth: 47.2 ″
Height units	47 U
Distance between levels as delivered	742 mm 29.2 ″
Number front doors	1
Number back doors	1
19" attachment	Front and rear 482.6 mm (19") Z-rail mounting sections, depth adjustable mounting
Design of rear door	Perforated Dual Door, Carbon Steel
Design for front door	Perforated Door, Carbon Steel
Load capacity	15,000 N

Features

Note	The door-opening angle may vary depending on site requirements or applications
Packaging unit	1 pc(s).
Customs tariff number	9403200082